

Cutting recommendation Kongsberg *

| Grade | Thickness | Table | Function | Tool | Bit/Blade type | Speed m/min | Acceleration | Pases |
|---------------------|-----------|-------------|-------------|-------------|-----------------|-------------|--------------|-------|
| KROMA Displayboard | 2.0 mm | Kongsberg C | Cut | RMKnife | BLD-SR8170 | 80 | 80 | 1 |
| KROMA Displayboard | 2.0 mm | Kongsberg C | Cut | CorruSpeed | BLD-SR8170 | 80 | 80 | 1 |
| KROMA Displayboard | 2.0 mm | Kongsberg C | Cut | Psaligraphy | BLD-SR6150 | 80 | 80 | 1 |
| KROMA Displayboard | 2.0 mm | Kongsberg C | V_Notch | HD_Bevel | Solid-BLD-SF245 | 80 | 80 | 1 |
| KROMA Displayboard | 2.0 mm | Kongsberg X | Cut | CorruSpeed | BLD-SR8172 | 50 | 100 | 1 |
| KROMA Displayboard | 2.0 mm | Kongsberg X | Cut | RMKnife | BLD-SR8172 | 50 | 100 | 1 |
| KROMA Displayboard | 2.0 mm | Kongsberg X | Cut | Psaligraphy | BLD-SR6150 | 40 | 60 | 1 |
| KROMA Displayboard | 2.0 mm | Kongsberg X | V_Notch | Bevel_Knife | Solid-BLD-SF245 | 50 | 100 | 1 |
| KROMA Displayboard | 2.5 mm | Kongsberg X | Cut | CorruSpeed | BLD-SR8170 | 80 | 100 | 1 |
| KROMA Displayboard | 2.5 mm | Kongsberg X | V_Cut | HD_Bevel | Solid-BLD-SF245 | 80 | 100 | 1 |
| KROMA Displayboard | 3.0 mm | Kongsberg C | Cut | RMKnife | BLD-SR8170 | 70 | 80 | 1 |
| KROMA Displayboard | 3.0 mm | Kongsberg C | Cut | Psaligraphy | BLD-SR6150 | 70 | 80 | 1 |
| KROMA Displayboard | 3.0 mm | Kongsberg C | Cut | CorruSpeed | BLD-SR8170 | 70 | 80 | 1 |
| KROMA Displayboard | 3.0 mm | Kongsberg C | V_Notch | HD_Bevel | Solid-BLD-SF245 | 70 | 80 | 1 |
| KROMA Displayboard | 3.0 mm | Kongsberg X | Cut | CorruSpeed | BLD-SR8170 | 50 | 100 | 1 |
| KROMA Displayboard | 3.0 mm | Kongsberg X | Cut | RMKnife | BLD-SR8170 | 50 | 100 | 1 |
| KROMA Displayboard | 3.0 mm | Kongsberg X | Cut | Psaligraphy | BLD-SR6150 | 50 | 100 | 1 |
| KROMA Displayboard | 3.0 mm | Kongsberg X | V_Notch | Bevel_Knife | Solid-BLD-SF245 | 50 | 100 | 1 |
| KROMA Displayboard | 5.0 mm | Kongsberg C | Cut | HFVibraCut | BLD-SR6315 | 15 | 50 | 1 |
| KROMA Displayboard | 5.0 mm | Kongsberg C | Cut | VibraCut | BLD-SR6315 | 25 | 50 | 1 |
| KROMA Displayboard | 5.0 mm | Kongsberg C | V_Notch | Bevel_Knife | Solid-BLD-SF245 | 70 | 80 | 1 |
| KROMA Displayboard | 5.0 mm | Kongsberg X | Cut | VibraCut | BLD-SR6315 | 10 | 100 | 1 |
| KROMA Displayboard | 5.0 mm | Kongsberg X | Cut | HFVibraCut | BLD-SR6315 | 10 | 100 | 1 |
| KROMA Displayboard | 5.0 mm | Kongsberg X | V_Notch | Bevel_Knife | Solid-BLD-SF245 | 50 | 100 | 1 |
| KROMA Displayboard | 5.0 mm | Kongsberg X | V_Notch | VI45_10 | BLD-DF562 | 30 | 80 | 1 |
| KROMA Displayboard | 5.0 mm | Kongsberg X | V_Notch | VI45_16 | BLD-DF572 | 30 | 80 | 1 |
| KROMA Kraft | 1.6 mm | Kongsberg X | Cut | CorruSpeed | BLD-SR8172 | 80 | 100 | 1 |
| KROMA Kraft | 1.6 mm | Kongsberg X | V_Notch | Bevel_Knife | Solid-BLD-SF245 | 80 | 100 | 1 |
| KROMA Kraft | 3.0 mm | Kongsberg C | Cut | RMKnife | BLD-SR8172 | 70 | 80 | 1 |
| KROMA Kraft | 3.0 mm | Kongsberg C | Cut | Psaligraphy | BLD-SR6150 | 70 | 80 | 1 |
| KROMA Kraft | 3.0 mm | Kongsberg C | Cut | CorruSpeed | BLD-SR8172 | 70 | 50 | 1 |
| KROMA Kraft | 3.0 mm | Kongsberg C | Partial_Cut | RMKnife | BLD-SR8172 | 80 | 80 | 1 |
| KROMA Kraft | 3.0 mm | Kongsberg C | V_Notch | HD_Bevel | Solid-BLD-SF245 | 20 | 50 | 1 |
| KROMA Kraft | 3.0 mm | Kongsberg X | Cut | CorruSpeed | BLD-SR8172 | 50 | 100 | 1 |
| KROMA Kraft | 3.0 mm | Kongsberg X | Cut | Psaligraphy | BLD-SR6150 | 50 | 100 | 1 |
| KROMA Kraft | 3.0 mm | Kongsberg X | Cut | RMKnife | BLD-SR8172 | 50 | 100 | 1 |
| KROMA Kraft | 3.0 mm | Kongsberg X | Partial_Cut | CorruSpeed | BLD-SR8172 | 50 | 100 | 1 |
| KROMA Kraft | 3.0 mm | Kongsberg X | V_Notch | Bevel_Knife | Solid-BLD-SF245 | 20 | 100 | 1 |
| KROMA Natural White | 3.0 mm | Kongsberg C | Cut | VibraCut | BLD-SR6315 | 20 | 80 | 1 |
| KROMA Natural White | 3.0 mm | Kongsberg C | Cut | HFVibraCut | BLD-SR6315 | 20 | 80 | 1 |
| KROMA Natural White | 3.0 mm | Kongsberg C | V_Notch | HD_Bevel | Solid-BLD-SF245 | 90 | 80 | 1 |
| KROMA Natural White | 3.0 mm | Kongsberg X | Cut | VibraCut | BLD-SR6315 | 10 | 100 | 1 |
| KROMA Natural White | 3.0 mm | Kongsberg X | Cut | HFVibraCut | BLD-SR6316 | 10 | 90 | 1 |
| KROMA Natural White | 3.0 mm | Kongsberg X | V_Notch | Bevel_Knife | Solid-BLD-SF245 | 50 | 100 | 1 |
| KROMA All White | 1.0 mm | Kongsberg C | Cut | RMKnife | BLD-SR8170 | 80 | 90 | 1 |
| KROMA All White | 1.0 mm | Kongsberg C | Cut | CorruSpeed | BLD-SR8170 | 70 | 90 | 1 |
| KROMA All White | 1.0 mm | Kongsberg C | Cut | Psaligraphy | BLD-SR6150 | 70 | 90 | 1 |
| KROMA All White | 1.0 mm | Kongsberg C | V_Notch | HD_Bevel | Solid-BLD-SF245 | 70 | 90 | 1 |
| KROMA All White | 1.0 mm | Kongsberg X | Cut | CorruSpeed | BLD-SR8170 | 50 | 100 | 1 |
| KROMA All White | 1.0 mm | Kongsberg X | Cut | RMKnife | BLD-SR8170 | 50 | 100 | 1 |
| KROMA All White | 1.0 mm | Kongsberg X | Cut | Psaligraphy | BLD-SR6150 | 50 | 100 | 1 |
| KROMA All White | 1.0 mm | Kongsberg X | Partial_Cut | CorruSpeed | BLD-SR8170 | 50 | 100 | 1 |
| KROMA All White | 1.0 mm | Kongsberg X | V_Notch | Bevel_Knife | Solid-BLD-SF245 | 50 | 100 | 1 |
| KROMA All White | 2.0 mm | Kongsberg C | Cut | RMKnife | BLD-SR8170 | 70 | 80 | 1 |
| KROMA All White | 2.0 mm | Kongsberg C | Cut | CorruSpeed | BLD-SR8170 | 70 | 80 | 1 |
| KROMA All White | 2.0 mm | Kongsberg C | Cut | Psaligraphy | BLD-SR6150 | 60 | 80 | 1 |
| KROMA All White | 2.0 mm | Kongsberg C | Partial_Cut | CorruSpeed | BLD-SR8170 | 80 | 60 | 1 |
| KROMA All White | 2.0 mm | Kongsberg C | V_Notch | HD_Bevel | Solid-BLD-SF245 | 70 | 80 | 1 |
| KROMA All White | 2.0 mm | Kongsberg X | Cut | CorruSpeed | BLD-SR8170 | 40 | 100 | 1 |
| KROMA All White | 2.0 mm | Kongsberg X | Cut | RMKnife | BLD-SR8170 | 50 | 100 | 1 |
| KROMA All White | 2.0 mm | Kongsberg X | Cut | Psaligraphy | BLD-SR6150 | 40 | 100 | 1 |
| KROMA All White | 2.0 mm | Kongsberg X | Partial_Cut | CorruSpeed | BLD-SR8170 | 50 | 100 | 1 |
| KROMA All White | 2.0 mm | Kongsberg X | V_Notch | Bevel_Knife | Solid-BLD-SF245 | 20 | 100 | 1 |
| KROMA All Black | 1.8 mm | Kongsberg C | Cut | CorruSpeed | BLD-SR8172 | 80 | 70 | 1 |
| KROMA All Black | 1.8 mm | Kongsberg C | Cut | RMKnife | BLD-SR8172 | 80 | 70 | 1 |
| KROMA All Black | 1.8 mm | Kongsberg C | Cut | Psaligraphy | BLD-SR6150 | 70 | 70 | 1 |
| KROMA All Black | 1.8 mm | Kongsberg C | Partial_Cut | CorruSpeed | BLD-SR8172 | 80 | 70 | 1 |
| KROMA All Black | 1.8 mm | Kongsberg C | V_Notch | HD_Bevel | Solid-BLD-SF245 | 30 | 80 | 1 |
| KROMA All Black | 1.8 mm | Kongsberg X | Cut | CorruSpeed | BLD-SR8172 | 40 | 100 | 1 |
| KROMA All Black | 1.8 mm | Kongsberg X | Cut | RMKnife | BLD-SR8172 | 40 | 100 | 1 |
| KROMA All Black | 1.8 mm | Kongsberg X | Cut | Psaligraphy | BLD-SR6150 | 40 | 100 | 1 |

| | | | | | | | | |
|---------------------|--------|-------------|-------------|-------------|-----------------|-----|-----|---|
| KROMA All Black | 1.8 mm | Kongsberg X | Partial_Cut | CorruSpeed | BLD-SR8172 | 50 | 100 | 1 |
| KROMA All Black | 1.8 mm | Kongsberg X | V_Notch | Bevel_Knife | Solid-BLD-SF245 | 25 | 100 | 1 |
| KROMA All Black | 3.0 mm | Kongsberg C | Cut | RMKnife | BLD-SR8170 | 70 | 70 | 1 |
| KROMA All Black | 3.0 mm | Kongsberg C | Cut | CorruSpeed | BLD-SR8170 | 70 | 70 | 1 |
| KROMA All Black | 3.0 mm | Kongsberg C | Cut | Psaligraphy | BLD-SR6150 | 70 | 70 | 1 |
| KROMA All Black | 3.0 mm | Kongsberg C | Partial_Cut | CorruSpeed | BLD-SR8170 | 100 | 80 | 1 |
| KROMA All Black | 3.0 mm | Kongsberg C | V_Notch | HD_Bevel | Solid-BLD-SF245 | 60 | 70 | 1 |
| KROMA All Black | 3.0 mm | Kongsberg X | Cut | CorruSpeed | BLD-SR8170 | 40 | 100 | 1 |
| KROMA All Black | 3.0 mm | Kongsberg X | Cut | RMKnife | BLD-SR8170 | 40 | 100 | 1 |
| KROMA All Black | 3.0 mm | Kongsberg X | Cut | Psaligraphy | BLD-SR6150 | 40 | 100 | 1 |
| KROMA All Black | 3.0 mm | Kongsberg X | Partial_Cut | CorruSpeed | BLD-SR8172 | 50 | 100 | 1 |
| KROMA All Black | 3.0 mm | Kongsberg X | V_Notch | Bevel_Knife | Solid-BLD-SF245 | 20 | 100 | 1 |
| KROMA Outdoor | 1.5 mm | Kongsberg C | Cut | RMKnife | BLD-DR8280A | 100 | 100 | 1 |
| KROMA Outdoor | 1.5 mm | Kongsberg C | Cut | Psaligraphy | BLD-DR6169A | 80 | 90 | 1 |
| KROMA Outdoor | 1.5 mm | Kongsberg C | Cut | CorruSpeed | BLD-DR8280A | 80 | 90 | 1 |
| KROMA Outdoor | 1.5 mm | Kongsberg C | V_Notch | HD_Bevel | Solid-BLD-SF245 | 100 | 100 | 1 |
| KROMA Outdoor | 1.5 mm | Kongsberg X | Cut | CorruSpeed | BLD-DR8280A | 50 | 100 | 1 |
| KROMA Outdoor | 1.5 mm | Kongsberg X | Cut | RMKnife | BLD-DR8280A | 50 | 100 | 1 |
| KROMA Outdoor | 1.5 mm | Kongsberg X | Cut | Psaligraphy | BLD-DR6169A | 50 | 100 | 1 |
| KROMA Outdoor | 1.5 mm | Kongsberg X | Partial_Cut | CorruSpeed | BLD-DR8280A | 50 | 100 | 1 |
| KROMA Outdoor | 1.5 mm | Kongsberg X | V_Notch | Bevel_Knife | Solid-BLD-SF245 | 50 | 100 | 1 |
| KROMA Mountingboard | 2.0 mm | Kongsberg C | Cut | RMKnife | BLD-SR8170 | 80 | 80 | 1 |
| KROMA Mountingboard | 2.0 mm | Kongsberg C | Cut | CorruSpeed | BLD-SR8170 | 80 | 80 | 1 |
| KROMA Mountingboard | 2.0 mm | Kongsberg C | Cut | Psaligraphy | BLD-SR6150 | 80 | 80 | 1 |
| KROMA Mountingboard | 2.0 mm | Kongsberg X | Cut | CorruSpeed | BLD-SR8170 | 50 | 100 | 1 |
| KROMA Mountingboard | 2.0 mm | Kongsberg X | Cut | RMKnife | BLD-SR8170 | 50 | 100 | 1 |
| KROMA Mountingboard | 2.0 mm | Kongsberg X | Cut | Psaligraphy | BLD-SR6150 | 50 | 100 | 1 |
| KROMA Mountingboard | 2.0 mm | Kongsberg X | Partial_Cut | CorruSpeed | BLD-SR8170 | 50 | 100 | 1 |
| EKA Board | 2.0 mm | Kongsberg C | Cut | VibraCut | BLD-SR6315 | 10 | 60 | 1 |
| EKA Board | 2.0 mm | Kongsberg C | Cut | HFVibraCut | BLD-SR6315 | 10 | 60 | 1 |
| EKA Board | 2.0 mm | Kongsberg X | Cut | VibraCut | BLD-SR6315 | 10 | 100 | 1 |
| EKA Board | 2.0 mm | Kongsberg X | Cut | HFVibraCut | BLD-SR6315 | 10 | 100 | 1 |
| EKA Board | 3.0 mm | Kongsberg C | Cut | VibraCut | BLD-SR6315 | 10 | 80 | 1 |
| EKA Board | 3.0 mm | Kongsberg C | Cut | HFVibraCut | BLD-SR6315 | 10 | 80 | 1 |
| EKA Board | 3.0 mm | Kongsberg X | Cut | VibraCut | BLD-SR6315 | 10 | 80 | 1 |
| EKA Board | 3.0 mm | Kongsberg X | Cut | HFVibraCut | BLD-SR6315 | 10 | 80 | 1 |
| Coaster Board | 0.9 mm | Kongsberg C | Cut | RMKnife | BLD-DR8260A | 70 | 80 | 1 |
| Coaster Board | 0.9 mm | Kongsberg C | Cut | Psaligraphy | BLD-DR6169A | 70 | 80 | 1 |
| Coaster Board | 0.9 mm | Kongsberg C | Cut | CorruSpeed | BLD-DR8260A | 70 | 80 | 1 |
| Coaster Board | 0.9 mm | Kongsberg C | Crease | Crease_26mm | 4 Point | 50 | 100 | 1 |
| Coaster Board | 0.9 mm | Kongsberg X | Cut | CorruSpeed | BLD-DR8260A | 50 | 100 | 1 |
| Coaster Board | 0.9 mm | Kongsberg X | Cut | RMKnife | BLD-DR8260A | 50 | 100 | 1 |
| Coaster Board | 0.9 mm | Kongsberg X | Cut | Psaligraphy | BLD-DR6169A | 50 | 100 | 1 |
| Coaster Board | 0.9 mm | Kongsberg X | Crease | Crease_26mm | 4 Point | 50 | 100 | 1 |
| Studiocard 2S | 0.6 mm | Kongsberg C | Cut | CorruSpeed | BLD-SR8170 | 100 | 100 | 1 |
| Studiocard 2S | 0.6 mm | Kongsberg C | Cut | RMKnife | BLD-SR8170 | 100 | 100 | 1 |
| Studiocard 2S | 0.6 mm | Kongsberg C | Cut | Psaligraphy | BLD-SR6150 | 100 | 100 | 1 |
| Studiocard 2S | 0.6 mm | Kongsberg C | Crease | Crease_26mm | 6 Point | 100 | 100 | 1 |
| Studiocard 2S | 0.6 mm | Kongsberg C | Partial_Cut | CorruSpeed | BLD-SR8170 | 100 | 100 | 1 |
| Studiocard 2S | 0.6 mm | Kongsberg X | Cut | CorruSpeed | BLD-SR8172 | 50 | 100 | 1 |
| Studiocard 2S | 0.6 mm | Kongsberg X | Cut | Psaligraphy | BLD-SR6150 | 50 | 100 | 1 |
| Studiocard 2S | 0.6 mm | Kongsberg X | Cut | RMKnife | BLD-SR8170 | 50 | 100 | 1 |
| Studiocard 2S | 0.6 mm | Kongsberg X | Crease | Crease_26mm | 6 Point | 50 | 100 | 1 |
| Studiocard 2S | 0.6 mm | Kongsberg X | Partial_Cut | CorruSpeed | BLD-SR8172 | 50 | 100 | 1 |

* These are guidelines, however, there can be many different blade and setting combinations